

Data Sheet

Surface mounted Power Double USB-C/A Socket PD/QC

Art. Nr. 67359000 (BP)

Art. Nr. 67359500 (SP)

07.08.2024

Input voltage: 8 - 30 V DC

Output USB-A:

Input voltage	Output voltage	Output current max.
12,0 V	5,0 V	2,2 A
	9,0 V	2,2 A
	12,0 V	1,9 A
24,0 V	5,0 V	2,2 A
	9,0 V	2,2 A
	12,0 V	1,9 A
	15,0 V	1,6 A
	20,0 V	1,2 A

Output USB-C:

Input voltage	Output voltage	Output current max.
12,0 V	5,0 V	3,0 A
	9,0 V	3,0 A
	12,0 V	2,5 A
24,0 V	5,0 V	3,0 A
	9,0 V	3,0 A
	12,0 V	2,5 A
	15,0 V	2,0 A
	20,0 V	1,5 A

Surface mounted Power Double USB-C/A Socket PD/QC

Art. Nr. 67359000 (BP)

Art. Nr. 67359500 (SP)

07.08.2024

USB-A and USB-C outputs are independent of each other and can be used individually or together.

Nominal output power according to PD and QC protocol:

USB-A (QC):	18 W
USB-C (PD):	30 W
Output Power max.:	30 W (output C) + 24 W (output A)
Protocol A socket:	Quick Charge (QC), PPS
Protocol C socket:	Power Delivery (PD), Quick Charge, PPS

Idle current:	max. 5 mA
Protection against:	short circuit, overload , overvoltage, overtemperature and reverse polarity

Material:

Housing:	ABS
Temperature stress:	max. 110 °C

Cable:

Strand:	2 x 0,5 mm ² red (+) / black (-)
Length:	150 mm

Surface mounted Power Double USB-C/A Socket PD/QC

Art. Nr. 67359000 (BP)

Art. Nr. 67359500 (SP)

07.08.2024

