

PRODUCT SPECIFICATION



Brand	C.K
Product Range	Xonic ESD Screwdrivers
Catalogue number	4838X, 4840X, 4875X, 4877X, 4880X, 4882X, 4883X, 4884X
Date	06/11/2008

Range Description
A range of Electronic screwdrivers with ESD protection

- Features**
- Ergonomically designed handle with hollow rotating cap for ease of use and precise control
 - Electro Statically Dissipative to protect sensitive electronic components
 - Blades made from premium quality Chrome Vanadium Molybdenum steel for strength
 - Tips accurately machined for the ultimate screw fit



Item Number	Item Description	EAN No	Commodity code	Carton Qty
T4838XESD15	Xonic ESD Screwdriver Hex 1.5 x 50mm	5013969981926	82054000	30
T4838XESD20	Xonic ESD Screwdriver Hex 2.0 x 50mm	5013969981933	82054000	30
T4838XESD25	Xonic ESD Screwdriver Hex 2.5 x 60mm	5013969981940	82054000	30
T4838XESD30	Xonic ESD Screwdriver Hex 3.0 x 60mm	5013969981957	82054000	30
T4840XESD32	Xonic ESD Nut Spinner 3.2 x 60mm	5013969978452	82054000	30
T4840XESD35	Xonic ESD Nut Spinner 3.5 x 60mm	5013969978469	82054000	30
T4840XESD40	Xonic ESD Nut Spinner 4.0 x 60mm	5013969978476	82054000	30
T4840XESD45	Xonic ESD Nut Spinner 4.5 x 60mm	5013969978520	82054000	30
T4840XESD50	Xonic ESD Nut Spinner 5.0 x 60mm	5013969978537	82054000	30
T4840XESD55	Xonic ESD Nut Spinner 5.5 x 60mm	5013969978544	82054000	30
T4875X ESD	Xonic ESD Screwdriver PZD0 x 60mm	5013969978667	82054000	30
T4875X ESD 1	Xonic ESD Screwdriver PZD1 x 80mm	5013969978674	82054000	30
T4877XESD04	Xonic ESD Screwdriver TX04 x 50mm	5013969978773	82054000	30
T4877XESD05	Xonic ESD Screwdriver TX05 x 50mm	5013969978780	82054000	30
T4877XESD06	Xonic ESD Screwdriver TX06 x 50mm	5013969978797	82054000	30
T4877XESD07	Xonic ESD Screwdriver TX07 x 50mm	5013969978810	82054000	30
T4877XESD08	Xonic ESD Screwdriver TX08 x 60mm	5013969978827	82054000	30
T4880XES08	Xonic ESD Screwdriver SL 0.8 x 60mm	5013969979299	82054000	30
T4880XES12	Xonic ESD Screwdriver SL 1.2 x 60mm	5013969979312	82054000	30
T4880XES15	Xonic ESD Screwdriver SL 1.5 x 60mm	5013969979329	82054000	30
T4880XES18	Xonic ESD Screwdriver SL 1.8 x 60mm	5013969979336	82054000	30
T4880XES256	Xonic ESD Screwdriver SL 2.5 x 60mm	5013969979343	82054000	30
T4880XES257	Xonic ESD Screwdriver SL 2.5 x 75mm	5013969979350	82054000	30
T4880XES310	Xonic ESD Screwdriver SL 3.0 x 100mm	5013969979367	82054000	20
T4880XES315	Xonic ESD Screwdriver SL 3.0 x 150mm	5013969979374	82054000	10
T4880XES410	Xonic ESD Screwdriver SL 4.0 x 100mm	5013969979398	82054000	20
T4880XES415	Xonic ESD Screwdriver SL 4.0 x 150mm	5013969979411	82054000	10
T4882X0 ESD	Xonic ESD Screwdriver PH0 x 60mm	5013969979497	82054000	30
T4882X000ES	Xonic ESD Screwdriver PH000 x 60mm	5013969979527	82054000	30
T4882X00ESD	Xonic ESD Screwdriver PH00 x 60mm	5013969979510	82054000	30
T4882X1 ESD	Xonic ESD Screwdriver PH1 x 80mm	5013969979534	82054000	30
T4883XESD	Xonic ESD Screwdrivers Set of 7	5013969983890	82054000	1
T4884X ESD	Xonic ESD Screwdrivers Set of 4	5013969981346	82054000	1

Technical product information	Handle materials electrostatically dissipative to DIN EN 61340 5,1 & 5,2
Standards compliance	None applicable
User health and safety information	None applicable

RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K Tools are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered
Country of origin	Germany

Dimensional details

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T4838XESD15	2,5	146	17	13	46	193	17	20
T4838XESD20	2,5	146	17	13	46	193	17	20
T4838XESD25	3,0	160	17	16	46	207	17	23
T4838XESD30	3,5	160	17	17	46	207	17	24
T4840XESD32	4,0	159	17	21	46	206	17	28
T4840XESD35	4,0	159	17	22	46	206	17	29
T4840XESD40	4,0	160	17	22	46	207	17	29
T4840XESD45	4,0	157	17	23	46	204	17	30
T4840XESD50	4,0	157	17	23	46	204	17	30
T4840XESD55	4,0	160	17	23	46	207	17	30
T4875X ESD	3,0	160	17	16	46	207	17	23
T4875X ESD 1	4,5	180	17	25	46	227	17	32
T4877XESD04	2,5	150	17	13	46	197	17	20
T4877XESD05	2,5	150	17	13	46	197	17	30
T4877XESD06	3,5	150	17	16	46	197	17	23
T4877XESD07	3,5	150	17	17	46	197	17	24
T4877XESD08	3,5	160	17	18	46	207	17	25
T4880XES08	2,5	157	17	13	46	204	17	20
T4880XES12	2,5	160	17	13	46	207	17	20
T4880XES15	2,5	157	17	13	46	204	17	20
T4880XES18	2,5	160	17	13	46	207	17	20
T4880XES256	2,5	160	17	14	46	207	17	21

T4880XES257	2,5	173	17	14	46	220	17	21
T4880XES310	3,0	198	17	17	46	245	17	24
T4880XES315	3,0	250	17	19	46	297	17	26
T4880XES410	4,0	200	17	23	46	247	17	30
T4880XES415	4,0	250	17	28	46	297	17	35
T4882X0 ESD	3,0	160	17	15	46	207	17	22
T4882X000ES	2,5	160	17	13	46	207	17	20
T4882X00ESD	2,5	160	17	13	46	207	17	20
T4882X1 ESD	4,5	180	17	24	46	227	17	31
T4883XESD				97	192	310	30	249
T4884X ESD				59	120	310	30	132

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T4838XESD15	245	125	65	684		
T4838XESD20	245	125	65	685		
T4838XESD25	245	125	65	757		
T4838XESD30	245	125	65	810		
T4840XESD32	245	125	65	916		
T4840XESD35	245	125	65	943		
T4840XESD40	245	125	65	951		
T4840XESD45	245	125	65	969		
T4840XESD50	245	125	65	962		
T4840XESD55	245	125	65	985		
T4875X ESD	245	125	65	754		
T4875X ESD 1	245	125	65	1048		
T4877XESD04	245	125	65	551		
T4877XESD05	245	125	65	669		

T4877XESD06	245	125	65	778		
T4877XESD07	245	125	65	784		
T4877XESD08	245	125	65	815		
T4880XES08	245	125	65	675		
T4880XES12	245	125	65	662		
T4880XES15	245	125	65	676		
T4880XES18	245	125	65	676		
T4880XES256	245	125	65	694		
T4880XES257	245	125	65	696		
T4880XES310	290	90	65	546		
T4880XES315	420	110	35	330		
T4880XES410	290	90	65	678		
T4880XES415	420	110	35	423		
T4882X0 ESD	245	125	65	722		
T4882X000ES	245	125	65	669		
T4882X00ESD	245	125	65	678		
T4882X1 ESD	245	125	65	1014		
T4883XESD						
T4884X ESD						

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T4838XESD15	7	Hanger					80	carton
T4838XESD20	7	Hanger					80	carton
T4838XESD25	7	Hanger					80	carton
T4838XESD30	7	Hanger					80	carton
T4840XESD32	7	Hanger					80	carton
T4840XESD35	7	Hanger					80	carton
T4840XESD40	7	Hanger					80	carton
T4840XESD45	7	Hanger					80	carton
T4840XESD50	7	Hanger					80	carton

T4840XESD55	7	Hanger					80	carton
T4875X ESD	7	Hanger					80	carton
T4875X ESD 1	7	Hanger					80	carton
T4877XESD04	7	Hanger					80	carton
T4877XESD05	7	Hanger					80	carton
T4877XESD06	7	Hanger					80	carton
T4877XESD07	7	Hanger					80	carton
T4877XESD08	7	Hanger					80	carton
T4880XES08	7	Hanger					80	carton
T4880XES12	7	Hanger					80	carton
T4880XES15	7	Hanger					80	carton
T4880XES18	7	Hanger					80	carton
T4880XES256	7	Hanger					80	carton
T4880XES257	7	Hanger					80	carton
T4880XES310	7	Hanger					72	carton
T4880XES315	7	Hanger					73	carton
T4880XES410	7	Hanger					72	carton
T4880XES415	7	Hanger					73	carton
T4882X0 ESD	7	Hanger					80	carton
T4882X000ES	7	Hanger					80	carton
T4882X00ESD	7	Hanger					80	carton
T4882X1 ESD	7	Hanger					80	carton
T4883XESD								
T4884X ESD								