

PRODUCT SPECIFICATION

**Carl
Kammerling**
International

Brand	C.K
Product Range	Dextro VDE Stubby Slim Screwdrivers
Catalogue number	48343, 48344, 48345
Date	26/01/2018

Range Description

A range of slim-shafted VDE approved professional electricians' stubby screwdrivers

Features

- Slim shafted insulated blades - allow access to recessed screws and fixings
- Cellulose acetate handles – shatterproof and wipe clean
- Non-roll handle design – specifically designed to stop the screwdrivers rolling off non-flat surfaces
- Tip type marking on the end of the handle for convenient blade type identification
- Toughened high alloy steel blade offering the ultimate in wear resistance and performance
- Molybdenum-vanadium-steel blade with black non-peel tip finish for corrosion protection
- Precision machined tips for the ultimate screw fit and high torque output



T48343-2



T48344-040



T48344-055



T48345-2



T48349

Item Number	Item Description	EAN No	Commodity code	Carton Qty
T48343-2	Stubby VDE Slim Screwdriver PZ2x46	5013969960921	8205400000	6
T48344-040	Stubby VDE Slim Screwdriver SL4.0x46	5013969960952	8205400000	6
T48344-055	Stubby VDE Slim Screwdriver SL5.5x46	5013969960969	8205400000	6

T48345-2	Stubby VDE Slim Screwdriver MOD2x46	5013969960976	8205400000	6
300004	Stubby VDE Slim Screwdriver Stand	N/A	73262000	1
T49398H	Stubby VDE Slim Screwdriver Stand Header	N/A	49111090	1
T48349	Stubby VDE Slim Screwdriver Set/4	5013969244595	82054000	20

Technical product information	Blade/Shaft Made from chrome molybdenum vanadium steel, hardened to 57-59 HRC, black non-peel finish. Handle The handle core is polypropylene, injection moulded around the blade with a TPE soft grip over-mould. The handles are shatterproof down to -35° C. Dimensions <table><tr><th>Dimensions (mm)</th><th>Handle length</th><th>Blade length</th><th>Blade Dia</th><th>Tip thickness</th></tr><tr><td>T48343-2</td><td>60</td><td>46</td><td>6.0</td><td>-</td></tr><tr><td>T48344-040</td><td>60</td><td>46</td><td>4.0</td><td>0.8</td></tr><tr><td>T48344-055</td><td>60</td><td>46</td><td>5.5</td><td>1.0</td></tr><tr><td>T48345-2</td><td>60</td><td>46</td><td>6.0</td><td>-</td></tr></table>	Dimensions (mm)	Handle length	Blade length	Blade Dia	Tip thickness	T48343-2	60	46	6.0	-	T48344-040	60	46	4.0	0.8	T48344-055	60	46	5.5	1.0	T48345-2	60	46	6.0	-
Dimensions (mm)	Handle length	Blade length	Blade Dia	Tip thickness																						
T48343-2	60	46	6.0	-																						
T48344-040	60	46	4.0	0.8																						
T48344-055	60	46	5.5	1.0																						
T48345-2	60	46	6.0	-																						
Standards compliance	Electrical safety Fully approved and independently audited by the German VDE institute to VDE 0682/201:2005 01 IEC 60900:2012 Dimensional and performance <i>Slotted screwdrivers – DIN ISO 2380</i> <i>PZD/SDV/PH Screwdrivers – DIN ISO 8764</i>																									
User health and safety information	Users and bystanders are advised to wear safety goggles																									
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations																									
Material safety data	None applicable																									
Warranty	Dextro Screwdrivers are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered																									
Country of origin	Germany																									

Dimensional details

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T48343-2	35	35	106	53	35	35	106	53
T48344-040	35	35	106	50	35	35	106	51
T48344-055	35	35	106	51	35	35	106	51
T48345-2	35	35	106	53	35	35	106	53
300004	160	250	245	2700	160	250	245	2700
T49398H	146	3	155	30	146	3	155	30
T48349	150	35	165	235	150	35	165	235

	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
Item	Length mm	Width mm	Depth mm	Gross weight g	No of cartons on base	Number of rows high
T48343-2	200	80	60	53g	6	4
T48344-040	200	80	60	53g	6	4
T48344-055	200	80	60	53g	6	4
T48345-2	200	80	60	53g	6	4
T48349	320	230	200	4950	30	5

Packaging waste details

	Primary Packaging				Secondary packaging			
Item	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T48343-2	-	-	-	-	-	-	200	Box
T48344-040	-	-	-	-	-	-	200	Box
T48344-055	-	-	-	-	-	-	200	Box
T48345-2	-	-	-	-	-	-	200	Box
T48349	15	Hanger	-	-	-	-	250	Box