



6-Ports USB (C + C + C + C + A + A) Desktop GaN Charger (140W/140W/45W/20W/18W/18W)

6-in-1 200W GaN Charging Kit

Advanced Charging Technology





Unleash 200W of Super Power

4 x USB-C & 2 x USB-A




USB-C 1/2
140W Max


USB-C 3
45W Max


USB-C 4
20W Max


USB-A 1/2
18W Max

Powered by GaN Tech



Weight



Size



Temperature



Operating
Frequency



Note: The internal structure is a rendering. Please refer to the actual product.

Quickly Charge 6 Devices at Once

Workplace Solution

Improves productivity and reduces cable clutter



Family-Friendly

One charger for all your devices



USB Power Delivery 3.1


140W
USB-C 1/2

Vention 140W USB-C Port



30 minutes
55%
MacBook Pro 16"

Ordinary 100W USB-C Port



30 minutes
43%
MacBook Pro 16"

Note: All data are from Vention Lab.
The data will be slightly different due to the change in objective
circumstances. Please refer to the actual product.

Power for 3 Laptops



Charging Guide

Single-Port



Two-Port



Three-Port



Five-Port



Six-Port



Safe & Certified



Temperature
protection



Short circuit
protection



Anti-interference
protection



Flame-retardant
protection



Over current
protection



Overvoltage
protection

Start Charging Right Out of the Box



Less Hassle More Productivity



Universal Compatibility

Laptops



Apple

MacBook Pro 14"/16"
MacBook Air 13"/15"



Huawei

MateBook X Pro
MateBook 14/13
MateBook D 15/14



Xiaomi

Mi Notebook 14
RedmiBook 15 Pro/14 Pro



Lenovo

Yoga C930
ThinkPad

Phones



Apple

iPhone 7-15 Series
iPhone SE



Huawei

Mate 60-30 Series
P50-30 Series/Nova 8-7/
Nova 7 Pro/7SE



Xiaomi

Xiaomi 13-10 Series
Redmi K50 Series
Redmi 10X
Redmi 9



Samsung

S22, S21, S21+, S20, S20+,
S10, S10+, Note9 ...

Tablets



Apple

iPad (10th generation)/
iPad Pro (6th generation)/
All iPad Series



Huawei

All MatePad Series

Game Consoles



Switch



Steam Deck

Note: Only list popular models; for more compatible devices,
please get in touch with customer service....

Specifications

Brand	Vention
Name	200W Desktop GaN Charging Kit
Model	FEN
Color	Black
Material	Flame-Retardant PC
Protocols (USB-C 1/2)	PD 3.1/PD 3.0/PPS/FCP/Apple 2.4A/SCP/QC 3.0
Protocols (USB-C 3)	PD 3.0/PPS/FCP/Apple 2.4A/SCP/QC 3.0
Protocols (USB-C 4)	PD 3.0/PPS/FCP/Apple 2.4A/QC 3.0
Protocols (USB-A 1/2)	FCP/Apple 2.4A/QC 3.0/AFC
Warranty	1 year
Packaging	Color box
Accessory	USB-C male to male 5A cable (1 m) x 1; C7 connector power cord (1.5 m) x 1



Note: All data are from Vention Lab.
Sizes above are manually measured. There might be slight tolerance.

What's in the Box



Note: Packing difference exists for different meters or batches.
The photo is for reference only.



200W Desktop GaN Charger

Technical Features

Charger

Color	Black
Interface	USB-A+C
Shell	PC
Input	100-240V~50/60Hz, 2.5A Max
Output	Output (USB-C 1/2): 5V= 3A; 9V= 3A; 12V= 3A; 15V= 3A; 20V= 5A ; 28V= 5A (140W Max) Output (USB-C 3): 5V= 3A; 9V= 3A; 12V= 3A; 15V= 3A; 20V= 2.25A (45W Max) Output (USB-C 4): 5V= 3A; 9V= 2.22A; 12V= 1.67A (20W Max) Output (USB-A 1/2): 5V= 3A; 9V= 2A; 12V= 1.5A (18W Max) Output (USB-C 1 + USB-C 2): 140W + 60W (200W Max) Output (USB-C 1 + USB-C 2 + USB-C 3 + USB-C 4 + USB-A 1 + USB-A 2): 45W PD + 45W PD + 45W PD + 20W PD + QC 18W + QC 18W (191W Max)
Protocols	Supported protocol (USB-C 1/2): PD 3.1/PD 3.0/PPS/FCP/Apple 2.4A/SCP/QC 3.0 Supported protocol (USB-C 3): PD 3.0/PPS/FCP/Apple 2.4A/SCP/QC 3.0 Supported protocol (USB-C 4): PD 3.0/PPS/FCP/Apple 2.4A/QC 3.0 Supported protocol (USB-A 1/2): FCP/Apple 2.4A/QC 3.0/AFC

Cable

Interface	USB-C
Electroplating process	Nickel-Plated
Shell	PVC
OD	4.6mm
Data transfer rates	Nickel-Plated
Rated power	100W PD (Max) (5A)
Length	1 m

Color	Art.No.	EAN Code
Black	FENB0-EU	6922794780057



Package Contents

200W Desktop GaN Charger x 1

Packaging Information

Packing Dimension	18*17*6.4cm
Packing Weight	0.986kg
Carton Dimension	48*29*31cm
Carton Qty	12pcs
Carton Weight	11.8kg

<https://ventiontech.com/>