



4-Ports USB (C + C + C + A) GaN Universal Travel Adapter (100W/100W/20W/18W)

Universal Travel Adapter

Explore the world, conquer business trips,
and ace your studies abroad—all with just one adapter.





GaN Technology



Safety 10A fuse



PD 100W Fast laptop charging



Compact and Worldwide use



AC + USB-C * 3 + USB-A 5 Devices charging simultaneousl

GaN Technology



Light as **287.5g** $\approx$ Mouse weight

Eight Layer Protection



Temperature
Protection



Over Current
Protection



Overvoltage
Protection



Overcharge
Protection



Under Voltage
Protection



Short Circuit
Protection



Overload
Protection



Chip
Protection

Note: The internal structure is a rendering. Please refer to the actual product.

PD 100W Fast Laptop Charging

USB-C2 Single Port

100W Max



USB-C1 Single Port

100W Max

Charge 2 Laptops at High Speed



Charge 5 Devices at Once

Save your clustered desktop.



1x 
8-hole AC

3x 
USB-C

1x 
USB-A

Total Output: **120.0W**

USB Power Output

Power up fast without risking your device with dynamic charging.

Single-port mode



USB-C1: **100W**



USB-C2: **100W**



USB-C3: **20W**



USB-A1: **18W**

Three-port mode



USB-C1 + C2 + C3:



65W + 35W



+ 20W



USB-C1 + C2 + A1:



65W + 35W



+ 18W



C2 + (C3 + A1):



35W + (5V $\Rightarrow$ 3A)



Dual-port mode



USB-C1 + USB-C2:



65W + 35W



USB-C1 + USB-C3:



65W + 20W



USB-C1 + USB-A1:



65W + 18W



USB-C2 + USB-C3:



35W + 20W



USB-C2 + USB-A1:



35W + 18W



USB-C3 + USB-A1:



5V $\Rightarrow$ 3A (15W)

Four-port mode



C1 + C2 + (C3 + A1):



65W + 35W



+ (5V $\Rightarrow$ 3A)



Upgraded 10A Fuse



Supports **2500W** power for various equipment.



laptop



hair dryer



kettle



induction cooker



fan



iron



desk lamp



razor



projector



Four Plug Types

An all-in-one charging solution.



Addressing all Your Charging Requirements

The adapter is compatible with most countries worldwide.

US plug



AU plug



UK plug



EU plug



2 pin plug China



3 pin plug China



Note: Please confirm that the rated voltage matches before using.

100-250V World-wide Voltage

The adapter is compatible with most countries worldwide.



Note:

1. AC appliances can be directly plugged in, with a maximum load capacity of 10A 2500W.
2. This product does not have a voltage conversion function. When using the AC interface, the device voltage needs to be consistent with the local voltage.

Easy to Use

Only one plug can be introduced at a time.



Attentions:

1. Please make sure that the button is reset when the button is pushed out and retracted to the bottom, and if the button is not reset, it means that the pug has not been pushed in place and will affect the normal use.
2. Only one plug-type can be used at one time by sliding the knob selection, other plug-pins are locked automatically.

Specifications

Brand	Vention
Name	4-Port USB (C + C + C + A) GaN Universal Travel Adapter (100W/100W/20W/18W) Black
Model	FJG
Color	Black
Interface	USB-A/USB-C * 3
Rated Output	100~250V~10A Max, 2500W Max
Single-port output mode	
USB-C1/C2	5.0V $\rightarrow$ 3.0A 15.0W, 9.0V $\rightarrow$ 3.0A 27.0W, 12.0V $\rightarrow$ 3.0A 36.0W, 15.0V $\rightarrow$ 3.0A 45.0W, 20.0V $\rightarrow$ 5.0A 100.0W.
USB-C3	5.0V $\rightarrow$ 3.0A 15.0W, 9.0V $\rightarrow$ 2.22A 20.0W, 12.0V $\rightarrow$ 1.67A 20.0W.
USB-A1	5.0V $\rightarrow$ 3.0A 15.0W, 9.0V $\rightarrow$ 2.0A 18.0W, 12.0V $\rightarrow$ 1.5A 18.0W.
Multiple-port output mode	
USB-C1 + C2	65.0W + 35.0W
USB-C1 + C2 + C3	65.0W + 35.0W + 20.0W
USB-C1 + C2 + A1	65.0W + 35.0W + 18.0W
C1 + C2 + (C3 + A1)	65.0W + 35.0W + (15.0W)
Total output	120.0W
Protocols	
USB-C1/C2	PD3.0/PPS/AFC/FCP Apple 2.4A
USB-C3	PD3.0/AFC/FCP/Apple 2.4A
USB-A1	QC3.0/AFC/FCP/Apple 2.4A
Shell	PC
Fire Rating	UL 94V-0
Packing	Color Box



Note: All data are from Vention Lab.

Sizes above are manually measured. There might be slight tolerance.

Packaging Display



Note: Packing difference exists for different meters or batches.
The photo is for reference only.



120W GaN Universal Travel Adapter

Technical Features		
Color	Black	
Interface	USB-A+C	
Shell	PC	
Rated output	100-250V~10A Max, 2500W Max	
Output/Single-Port	C1/C2: 5.0V= 3.0A 15.0W,9.0V= 3.0A 27.0W,12.0V= 3.0A 36.0W. 15.0V= 3.0A 45.0W,20.0V= 5.0A 100.0W. C3:5.0V= 3.0A 15.0W,9.0V= 2.22A 20.0W,12.0V= 1.67A 20.0W. A1: 5.0V= 3.0A 15.0W,9.0V= 2.0A 18.0W,12.0V= 1.5A 18.0W.	
Output/Two-Ports	C1+C2 output mode: C1: 5.0V= 3.0A 15.0W,9.0V= 3.0A 27.0W,12.0V= 3.0A 36.0W,15.0V= 3.0A 45.0W, 20.0V= 3.25A 65.0W. C2: 5.0V= 3.0A 15.0W,9.0V= 3.0A 27.0W,15.0V= 2.33A 35.0W,20.0V= 1.75A 35.0W.	
Output/Three-Ports	C1+C2+C3 output mode: C1: 5.0V= 3.0A 15.0W,9.0V= 3.0A 27.0W,12.0V= 3.0A 36.0W,15.0V= 3.0A 45.0W, 20.0V= 3.25A 65.0W. C2: 5.0V= 3.0A 15.0W,9.0V= 3.0A 27.0W,15.0V= 2.33A 35.0W,20.0V= 1.75A 35.0W. C3: 5.0V= 3.0A 15.0W,9.0V= 2.22A 20.0W,12.0V= 1.67A 20.0W. C1+C2+A1 output mode: C1: 5.0V= 3.0A 15.0W,9.0V= 3.0A 27.0W,15.0V= 3.0A 45.0W,20.0V= 3.25A 65.0W C2: 5.0V= 3.0A 15.0W,9.0V= 3.0A 27.0W,15.0V= 2.33A 35.0W,20.0V= 1.75A 35.0W. A1: 5.0V= 3.0A 15.0W,9.0V= 2.0A 18.0W,12.0V= 1.5A 18.0W.	
Output/Four-Ports	C1+C2+C3+A1 output mode: C1: 5.0V= 3.0A 15.0W,9.0V= 3.0A 27.0W,12.0V= 3.0A 36.0W,15.0V= 3.0A 45.0W, 20.0V= 3.25A 65.0W. C2: 5.0V= 3.0A 15.0W,9.0V= 3.0A 27.0W,15.0V= 2.33A 35.0W,20.0V= 1.75A 35.0W. C3+A1: 5.0V= 3.0A 15.0W.	
Total DC Output	120.0W	
Protocols	USB C1/C2: PD3.0/PPS/AFC/FCP/Apple 2.4A USB C3: PD3.0/AFC/FCP/Apple 2.4A USB A1: OC3.0/AFC/FCP/Apple 2.4A	
Color	Art.No.	EAN Code
Black	FJGB0	6922794784710



Package Contents

120W GaN Universal Travel Adapter x 1

Packaging Information

Packing Dimension	12*8*5.5cm
Packing Weight	0.331kg
Carton Dimension	48*29*31cm
Carton Qty	50pcs
Carton Weight	16.5kg