


plating item 1	part no.
GOLD FLASH over NICKEL	131A13059X
30µin HARD GOLD over min. 50µin NICKEL	131C13059X

3	1	RETAINING RING	COPPER ALLOY	NICKEL PLATED
2	1	REAR SIDE	COPPER ALLOY	TIN PLATED
1	1	MATING SIDE	COPPER ALLOY	SEE TABLE
pos	qty	description	material	plating

Stückliste				
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	DO NOT ALTER CAD DRAWING BY HAND		tolerance	dim. in mm
	3 x b	A 6216	30.06.2016	Unkrüer
	a	Original		
	rev.	description	date	name
scale: 5:1		material: SEE PARTLIST		
title:		HIGH POWER CONTACT MALE		
		SOLDER PIN 90° / Ø3,2 / 30A		
		D-SUB COMBINATION		
dwg no:		13K1A365A		DIN-A3
part no:		SEE TABLE		

CONEC®

RoHS compliant