



STRIPPING DIMENSION



Directive 2002/95/EC RoHS compliant

3	1	RETAINING RING	COPPER ALLOY	NICKEL PLATED
2	1	REAR SIDE	COPPER ALLOY	GOLD FLASH over NICKEL
1	1	FRONT SIDE	COPPER ALLOY	min. 30µin HARD GOLD over min. 50µin NICKEL
pos	qty	description	material	plating
partlist				
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH			tolerance	scale: 5:1
			ISO 2768-m	material: SEE PARTLIST
			dim. in mm	title:
			drawn 30.01.12 Henneboel	HIGH POWER CONTACT MALE SOLDER CUP 10A FOR AWG 16-20; d=1,8mm D-SUB COMBINATION PREMATING
			appd. 30.01.12 Koch	
			norm	
DO NOT ALTER CAD DRAWING BY HAND			d-old	dwg no:
			a Original	DIN-A3
rev.	description	date	name	sh: 1
13K1A3886				part no: 131C10119X

CONEC