




(b)

plating	part no.
GOLD FLASH over NICKEL	131A13009X
30µin HARD GOLD over min. 50µin NICKEL	131C13009X

3	1	RETAINING RING	COPPER ALLOY	NICKEL PLATED
2	1	MATING SIDE	COPPER ALLOY	SEE TABLE
1	1	REAR SIDE	COPPER ALLOY	TIN PLATED
pos	qty	description	material	plating

partlist					scale:		10:1	
tolerance					material:		SEE PARTLIST	
dim. in mm					title:		HIGH POWER CONTACT MALE	
drawn					SOLDER PIN 90° 15A		D-SUB COMBINATION	
appd.					dwg no:		13K1A1164	
norm					DIN-		A3	
d-old					sh: 1		SEE TABLE	
1 x b					part no:		SEE TABLE	
a					rev.		description	
rev.					date		name	

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

date	name
29.06.04	Lehmenkühler
29.06.04	Mickenbecker
	norm
	d-old
1 x b	A4554
a	Original
rev.	description
date	name

CONEC