







STRIPPING DIMENSION



Directive 2002/95/EC
„RoHS“
Compliant

3	1	MATING SIDE	COPPER ALLOY	min. 8µin HARD GOLD over min. 50µin NICKEL
2	1	RETAINING RING	COPPER ALLOY	NICKEL PLATED
1	1	REAR SIDE	COPPER ALLOY	min. 8µin HARD GOLD over min. 50µin NICKEL
POS	QTY	DESCRIPTION	MATERIAL	PLATING

PARTLIST

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND				tolerance		 dim. in mm	scale: 5:1					
							material: SEE TABLE					
								date	name	title: HIGH POWER CONTACT FEMALE CRIMP / SOLDER VERSION 90° - 30A D-SUB COMBINATION		
								drawn	02.08.10			Petker
								appd.	02.08.10			Fischer
								norm				
								d-old		dwg no: Inventor DIN-A3		
										13K2A658		
										sh: 1		
rev.	description	date	name			part no: 132A16039X						