



used for:	D-SUB
-----------	-------



Wire size AWG	Crimp height A
28	0,61 – 0,76
26	0,66 – 0,81
24	0,66 – 0,86



STRIPPING DIMENSIONS (b)





Directive 2002/95/EC RoHS compliant

⑥ TECHNICAL DATA:

Material Stamped Contacts: Phosphor Bronze
Finish: Gold Flash over Nickel in the Contact Area
Temperature Range: -55°C to +125°C
Rated Current: 7.5A
Test Voltage: 1000V eff. at 50Hz
Contact Resistance: $\leq 10\text{m}\Omega$
Insulation Resistance: $\geq 5000\text{M}\Omega$
Crimping: Use Crimp Tool 360X10079X

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

				tolerance			
				2002	date	name	
				drawn	22.02.	Parei	
				appd.	22.02.	E. Mickenbecker	
				norm			
				d-old			
3 x b	Ä 4116	27.09.2011	Lehmen.				
a	Original						
rev.	description	date	name				



scale:	5:1
material:	SEE NOTES

title:	SOCKET CONTACT CRIMP AWG 28-24
--------	--------------------------------------

dwg no:	AutoCAD 2006	DIN-A
16K1A500		4
		sh: 1/1
part no: 162A11889X		