

6

5

4

3

2

1

used for:

D-SUB

H

H

G

G

F

F

E

E

D

D

C






C

B

B

A

A



NOTES:

1. METALSHELLS: STEEL; min. 320pin TIN
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY
PLATING: 8pin HARD GOLD OVER min. 50pin NICKEL
4. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
5. CONNECTOR IS PART MARKED: 163A50049X CONEC ABC

ROHS compliant, exemption 6c/
ROHS konform, Ausnahme 6c

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

2 x b	Ä 2141	30.12.2004	Lehmen
rev.	description	date	name

tolerance
0 ± 0.50 mm
0,0 ± 0.25 mm
0,00 ± 0.10 mm
± 15°



dim. in mm

scale:
material:

2:1 (5:1)

SEE NOTES

title:

ADAPTER
PLUG / SOCKET 50pos.
4-40 UNC

dwg no:

AutoCAD 2004

DIN-A

3

sh: 1/1

part no:

163A50049X

CONEC