





15-50pos.



9pos. = 1 x FULL METAL SCREW
15-50pos. = 2 x FULL METAL SCREW



1 x CABLE CLAMP / VERSION 1



1 x CABLE CLAMP / VERSION 2

	(b)		(b)			
No. of pos.	A $\pm$ 0.1	B	C $\pm$ 0.2	D	ϕ E	Part No.
9	31.20	25.0	37.95	15.0	8.0	165X00779A
15	39.52	33.3	38.95	15.0	9.0	165X00789A
25	53.42	47.0	38.95	15.0	11.0	165X00799A
37	69.70	63.5	38.95	15.0	11.0	165X00809A
50	67.30	61.1	38.95	19.0	14.5	165X00819A

HOOD: PC GF 20 UL 94 V-0; BLACK
FULL METAL SCREW: Ms 58 HARD; NICKEL PLATED
CABLE CLAMP: Cu Ni 18 Zn 20
SCREW FOR CABLE CLAMP: STEEL; NICKEL PLATED

Directive 2002/95/EC
"RoHS"
Compliant

APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
NOT ALTER CAD DRAWING BY HAND

5 x b	Ä 2343	12.10.2005	Lehmer
rev.	description	date	name

1:1

	title:
--	--------

9 - 50 pos.

shielded version black with metal screw

dwg no:	
---------	--

AutoCAD 2000	DIN-A
--------------	-------

16K1A284A

3
sh: 1/1

part no: SEE TABLE