



NOTES: (b)

- HOOD + COVER: PBT UL 94 V-0; BLACK
- CABLE STRAIN RELIEF: STEEL; NICKEL PLATED
- PRESS INSERT: ABS UL 94 V-0; BLACK
- SHORT SCREWS: BRASS; NICKEL PLATED (c)
- COVER SCREWS: STEEL; NICKEL PLATED
- LENS HEAD SCREWS: STEEL; NICKEL PLATED

TECHNICAL DATA:

- TEMPERATURE RANGE: - 40°C to + 125°C



CABLE STRAIN RELIEF (1x)




LENS HEAD SCREW (2x)




SHORT SCREW (2x)



PRESS INSERT (1x)



COVER SCREW (2x)



ROHS compliant, exemption 6c/
ROHS konform, Ausnahme 6c

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

1 x c	Ä21-0233	07.06.2024	JLE	d-old	16K1A707
5 x b	A5607	14.04.15	M.H.		
a	Original				
rev.	description	date	name		

tolerance



scale: 2:1
material: SEE NOTES

title: PLASTIC HOOD
37pos.
with straight cable exit

dwg no: (b) 16K1A3621

part no: (b) 165X13399X

DIN-
A3
sh: 1

CONEC®