





NOTES:

1. METALHOOD + COVER: ABS UL 94 V-0; METALLIZED
2. CABLE STRAIN RELIEF: STEEL; NICKEL PLATED
3. PRESS INSERT: ABS UL 94 V-0; METALLIZED
4. SHORT SCREWS: BRASS; NICKEL PLATED
5. LENS HEAD SCREWS: STEEL; NICKEL PLATED

TECHNICAL DATA:

- TEMPERATURE RANGE: - 33°C to + 90°C

ROHS compliant, exemption 6c/
ROHS konform, Ausnahme 6c

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale: 2:1				
							material: SEE NOTES				
								date	name	title: PLASTIC HOOD 9pos. with straight cable exit	
								drawn 03.09.2014	Unkrüer		
								appd. 04.09.2014	Lehmenkühler		
				norm							
1 x c	Ä21-0233	06.06.2024	JLE	d-old	16K2A171A			dwg no:	DIN- A3 sh: 1		
3 x b	Ä 5304	03.09.2014	Unkrüer					part no: 165X13469X			
a	Original										
rev.	description	date	name								

CONEC