

4-40 UNC

16,3

54,9

52,5

Ø12

47

54,9

CONEC

b



CABLE STRAIN RELIEF (1x)



LENS HEAD SCREW (2x)





SHORT SCREW (2x)



PRESS INSERT (1x)



COVER SCREW (2x)



b

NOTES:

1. HOOD + COVER: ABS UL 94 V-0; METALLIZED
2. CABLE STRAIN RELIEF: STEEL; NICKEL PLATED
3. PRESS INSERT: ABS UL 94 V-0; METALLIZED
4. SHORT SCREWS: BRASS; NICKEL PLATED
5. COVER SCREWS: STEEL; NICKEL PLATED
6. LENS HEAD SCREWS: STEEL; NICKEL PLATED

TECHNICAL DATA:

- TEMPERATURE RANGE: - 33°C to + 90°C

ROHS compliant, exemption 6c/
ROHS konform, Ausnahme 6c

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

1 x c	Ä21-0233	06.06.2024	JLE
3 x b	Ä 5304	03.09.2014	Unkrüer
a	Original		
rev.	description	date	name

CONEC

PLASTIC HOOD
25pos.
with straight cable exit

b 16K1A3495

165X13489X