




6		5		4		3		2		1																																																	
										used for: D-SUB																																																	
H																																																											
G																																																											
F																																																											
E																																																											
D																																																											
C																																																											
B																																																											
A																																																											
9pos.																																																											
15-50pos.																																																											
																																																											
																																																											
																																																											
3 x SCREW FOR CABLE CLAMP																																																											
1 x CABLE CLAMP / VERSION 1																																																											
1 x CABLE CLAMP / VERSION 2																																																											
9pos. = 1 x METAL SCREW WITH PLASTIC HEAD																																																											
15-50pos. = 2 x METAL SCREW WITH PLASTIC HEAD																																																											
<table><tr><th>No. of pos.</th><th>A±0.1</th><th>B</th><th>C±0.2</th><th>D</th><th>ØE</th><th>Part No. Bulk package</th><th>Part No. Single package</th></tr><tr><td>9</td><td>31.20</td><td>25.0</td><td>37.95</td><td>15.0</td><td>8.0</td><td>165X16019X</td><td>165X16019XE</td></tr><tr><td>15</td><td>39.52</td><td>33.3</td><td>38.95</td><td>15.0</td><td>9.0</td><td>165X16029X</td><td>165X16029XE</td></tr><tr><td>25</td><td>53.42</td><td>47.0</td><td>38.95</td><td>15.0</td><td>11.0</td><td>165X16039X</td><td>165X16039XE</td></tr><tr><td>37</td><td>69.70</td><td>63.5</td><td>38.95</td><td>15.0</td><td>11.0</td><td>165X16049X</td><td>165X16049XE</td></tr><tr><td>50</td><td>67.30</td><td>61.1</td><td>38.95</td><td>19.0</td><td>14.5</td><td>165X16059X</td><td>165X16059XE</td></tr></table>												No. of pos.	A±0.1	B	C±0.2	D	ØE	Part No. Bulk package	Part No. Single package	9	31.20	25.0	37.95	15.0	8.0	165X16019X	165X16019XE	15	39.52	33.3	38.95	15.0	9.0	165X16029X	165X16029XE	25	53.42	47.0	38.95	15.0	11.0	165X16039X	165X16039XE	37	69.70	63.5	38.95	15.0	11.0	165X16049X	165X16049XE	50	67.30	61.1	38.95	19.0	14.5	165X16059X	165X16059XE
No. of pos.	A±0.1	B	C±0.2	D	ØE	Part No. Bulk package	Part No. Single package																																																				
9	31.20	25.0	37.95	15.0	8.0	165X16019X	165X16019XE																																																				
15	39.52	33.3	38.95	15.0	9.0	165X16029X	165X16029XE																																																				
25	53.42	47.0	38.95	15.0	11.0	165X16039X	165X16039XE																																																				
37	69.70	63.5	38.95	15.0	11.0	165X16049X	165X16049XE																																																				
50	67.30	61.1	38.95	19.0	14.5	165X16059X	165X16059XE																																																				
NOTES: HOOD: PC GF 20 UL 94 V-0; GREY CABLE CLAMP: COPPER ALLOY SCREW FOR CABLE CLAMP: STEEL; NICKEL PLATED																																																											
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND																																																											
tolerance																																																											
dim. in mm																																																											
scale: 1:1																																																											
material: SEE NOTES																																																											
title: PLASTIC HOOD 9-50pos. unshielded version, grey with metal screw, with plastic head																																																											
dwg no: 16K1A2851																																																											
part no: SEE TABLE																																																											
DIN-A 3 sh: 1/1																																																											
Directive 2002/95/EC RoHS compliant																																																											
6		5		4		3		2		1																																																	