





used for: D-SUB


9pos.

15-50pos.




3 x SCREW FOR CABLE CLAMP

9pos. = 1 x FULL METAL SCREW
15-50pos. = 2 x FULL METAL SCREW



1 x CABLE CLAMP / VERSION 1



1 x CABLE CLAMP / VERSION 2

Directive 2002/95/EC
"RoHS"
Compliant

No. of pos.	A±0.1	B	C±0.2	D	ØE	Part No: Bulk package	Part No: Single package
9	31.20	25.0	37.95	15.0	8.0	165X16169X	165X16169XE
15	39.52	33.3	38.95	15.0	9.0	165X16179X	165X16179XE
25	53.42	47.0	38.95	15.0	11.0	165X16189X	165X16189XE
37	69.70	63.5	38.95	15.0	11.0	165X16199X	165X16199XE
50	67.30	61.1	38.95	19.0	14.5	165X16209X	165X16209XE

NOTES:

HOOD: PC GF 20 UL 94 V-0; GREY

FULL METAL SCREW: Ms 58 HARD; NICKEL PLATED

CABLE CLAMP: Cu Ni 18 Zn 20

SCREW FOR CABLE CLAMP: STEEL; NICKEL PLATED

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL
CUSTOMER APPROVAL DATE:
NAME: TITLE:
COMPANY NAME:
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY, WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Origin		

tolerance	dim. in mm
2010	date
drawn	20.04.
appd.	20.04.
norm	DIN 41652
d-old	
CONEC®	

scale:	1:1
material:	SEE NOTES
title:	PLASTIC HOOD 9-50pos. shielded version grey with metal screw
dwg no:	AutoCAD 2006
part no:	SEE TABLE