








NOTES:

1. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
4. NO CONTACTS ON POS. A1 - A4
5. CONNECTOR IS PART MARKED: 3009W4PAM99A10X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH															
DO NOT ALTER CAD DRAWING BY HAND				tolerance		 dim. in mm		scale: 2:1 (5:1)							
				material: SEE NOTES											
				title: D-SUB COMBINATION MALE 9W4P SOLDER CUP											
												date		name	
												drawn 28.04.14		Henneboel	
appd. 29.04.14		Lehmenkühler		dwg no:				DIN-A3 sh: 1							
norm															
d-old															
a Original															
rev.		description								date		name			
								part no: 3009W4PAM99A10X							

CONEC