




NOTES:

1. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
4. NO CONTACT ON POS. A1
5. CONNECTOR IS PART MARKED: 3011W1PAM99A10X CONEC ABC



Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance		dim. in mm	scale: 2:1 (5:1)	
				date	name		material: see notes	
				drawn	13.01.11	Schmidt	title: D-SUB COMBINATION MALE 11W1P SOLDER CUP	
				appd.	13.01.11	Koch		
				norm				
				d-old			dwg no:	
a	Origin			CONEC [®]			13K1A3542	
rev.	description	date	name				part no: 3011W1PAM99A10X	

DIN-A3	
sh: 1	