


NOTES:

- 1. METAL SHELLS: STEEL; min. 320µ" TIN
- 2. INSULATORS: PBT GF UL 94 V-0, BLACK
- 3. CONNECTOR IS PART MARKED: 3017W5SXXK99A10X CONEC ABC



APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL

CUSTOMER APPROVAL DATE:

NAME: TITLE: COMPANY NAME:

APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GMBH DO NOT ALTER CAD DRAWING BY HAND

|       |        |              |            |           |           |                                               |
|-------|--------|--------------|------------|-----------|-----------|-----------------------------------------------|
| 2004  | date   | name         | dim. in mm | tolerance | scale:    | 2:1                                           |
| drawn | 15.10. | Schmidt      |            |           | material: | SEE NOTES                                     |
| appd. | 15.10. | Mickenbecker |            |           | title:    | D-SUB COMBINATION FEMALE<br>17W5S CRIMP STYLE |
| norm  |        |              |            |           | dwg no:   | AutoCAD 2004 DIN-A<br>3<br>13K1A1258          |
| d-old |        |              |            |           | part no:  | 3017W5SXXK99A10X                              |

**CONEC®**