








NOTES:

1. METALSHELLS: STEEL, TIN PLATED
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
PLATING: min. 8µ" HARD GOLD OVER min. 50µ" NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
4. CONNECTOR IS PART MARKED: 3024W7SAM99A10X CONEC Y /WW
5. = CHECK DIMENSION

APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACON # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACON # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION OWNERSHIP AND COPYRIGHT OF CONEC GMBH DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name

tolerance		scale:	2:1
dim. in mm	name	material:	SEE NOTES
date	name	title:	D-SUB COMBINATION FEMALE
drawn	13.05.	Mankopf	24W7S SOLDER CUP
appd.	13.05.	Kühle	
norm			
d-old			

Directive 2002/95/EC
"RoHS"
Compliant



dwg no:	AutoCAD 2000	DIN-A
	13K1A852	3
		sh: 1/1
part no:	3024W7SAM99A10X	

used for: D-SUB COMBINATION