






PCB hole drillings
(PCB top side)
Leiterplattenbohrbild
(Leiterplatten Oberseite):



		dim. in mm		D-SUB Combination female 36W4S with threaded insert, metal bracket and PCB snap	
general tolerance/ Allgemeintoleranz:	0	± 0,50 mm	Date/Datum	Name	D-SUB Combination Buchsenleiste 36W4S mit Gewindeinsatz, Metallwinkel und PCB Clip
	0,0	± 0,25 mm	drawn/ gezeichnet	20.12.2022 Bub	
	0,00	± 0,10 mm	appd./ gepr.	20.12.2022 Henneboel	
Index: a Original	scale/stab: 2:1		dwg no / Z.-nr.: 13K1A6427		DIN-A3
RoHS compliant/ konform		CONEC®		2 / 2	