



Technical specification :


Rated voltage:	60 V
IEC 61076-2-101	
Current rating:	3 A at 40°C
IEC 61076-2-101	
Insulation resistance:	>=100 M
IEC 60512	
Pollution degree:	3/2
IEC 60664-1	
Degree of protection:	IP 67, in mated condition
IEC 60529	
Temperature range:	-30°C ... +80°C
EN 60512-11-10	
EN 60512-11-4	-40°C ... +85°C
Mating cycles:	>=100
IEC 60512-9a	

Materials:

Contact:	CuZn, Ni b / Au 0,2 gal.
Contact carrier:	PA, UL 94 V-0
Sealing:	FPM
Coupling nut/ screw:	GD-Zn, Nickel plated
Moulding body:	TPU, UL 94 HB, grey

Installation specification:

Recommended torque M12x1:	0,6 Nm
Recommended torque M8x1:	0,4 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 13: 36-000220 Insert across flats 9: 36-000210




Part no:	Description:
43-05185	SAL - 12 - YS4 - 8 - 2YK3

DO NOT ALTER CAD DRAWING BY HAND

RoHS & REACH compliant

general tolerance:	0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm * ± 5°	
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH		



dim. in mm

	date	name
drawn	09.11.15	Willer
appd.	09.11.15	Franz

CONEC®

title:

Y-splitter, male connector M12x1 - 2x
female connector M12x1

dwg no:

43K1A3172

part no:

see table