




Directive 2011/65/EU RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	DO NOT ALTER CAD DRAWING BY HAND				finish: Nickel plated			tolerance		 dim. in mm	scale: 5:1		material: COPPER ALLOY	
						date	name		title: HEX BOLT 4-40 UNC / M3 12mm long					
					drawn	28.08.14	Henneboel							
					appd.	28.08.14	Fischer							
					norm									
					d-old									
	a	Original								dwg no:		DIN-A4		
	rev.	description	date	name						740KEG1A		sh: 1		
											part no:		740-320170	