




POS.	A	B	C	D	E	F	Part NO.
9	30.80	16.92	25.00	19.20	11.08	8.31	DLS1XP4AA35X
15	39.20	25.25	33.30	27.70	19.39	16.62	DLS2XP4AA35X
25	53.10	38.96	47.10	41.10	33.24	30.47	DLS3XP4AA35X
37	69.40	55.42	63.50	57.30	49.86	47.09	DLS4XP4AA35X




SEE NOTE 4

used for: D-SUB



P.C.B. HOLE DRILLINGS



APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0, BLACK
- CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over min. 50µin NICKEL
- CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

			tolerance		dim. in mm
1 x b	Ä5446	04.12.2014	K.H.		
a	Original				
rev.	description	date	name		

CONEC®

scale:	2:1
material:	SEE NOTES
title:	D-SUB MALE 9-37pos. PCB STRAIGHT STAMPED CONTACTS with threaded spacer clip
dwg no:	AutoCAD 2004 16K1A1954
part no:	SEE TABLE

DIN-A
4
sh: 1/1