

TECHNICAL SPECIFICATION & PRODUCT DESCRIPTION

Winding wire DN2E 200 Ø 1,90 mm Mass: 250g

We offer round insulated copper wire, with two layers of enamel insulation with a nominal diameter of **Ø 1,90 mm**. Due to its outstanding performance, it is an excellent choice for any professional who relies on perfect quality, reliability and convenience of use. This flexible, well-laying, resistant to surrounding conditions and user-oriented product is ideal for even the most advanced production projects and any assembly, service and hobby work.

Wire technical parameters:

• Nominal wire conductor diameter	Ø 1,90 mm
• Conductor cross-section area CSA	2,85 mm²
• Wire conductor size in SWG system	SWG 15
• Manufacturer part number BQ MPN	DN2E1.90/0.25
• Product normative classification	EI/AIW Class 200 Grade 2
• Conductor base material	Copper Cu
• Inner layer of insulating enamel coating	2 x Polyester amide THEIC
• Outer layer of insulating enamel coating	2 x Polyamidoimid coat
• Min. outer diameter of insulated wire	Ø 1,975 mm
• Max. outer diameter of insulated wire	Ø 2,012 mm
• Minimum wire elongation at break	33 %
• Resistance to vibration, oscilation, overload	YES
• Resistance to aggressive chemical agents	YES
• Resistance to current and thermal shocks	YES
• Resistance to flame propagation	YES – Self - extinguishing type
• Method of electrical assembly and connecting	Soldering, Crimping, Welding
• Operating temperature range of winding wire	- 65°C ÷ + 200°C
• Wire thermoplasticity temperature	> + 350°C
• Insulation layer breakdown voltage	> 7,5 kV
• Quantity of product in package - net. weight	250 grams
• Approximate length of wire in package	9 meters
• Wire packaging system	Evenly wound on the spool

- Packaging material and dimensions - spools **Polypropylene Ø = 50mm / H = 42mm**
- Packaging logistical security **Thermo - shrinkable POF film cover**

We guarantee constant availability of items in stock and immediate shipping !

DN2E 200 double-enameled winding wires with the **BQ** logo guarantee not only the world's highest quality products and the latest environmentally friendly technologies, but also ensure comfort of use and savings resulting from reliability.

These wires are classified as **EI/AIW Class 200 Grade 2**, which means a double enameled insulation composed of polyesterimide and polyamide with an operating temperature in a very wide range from **-65°C** up to **+200°C**. The use of such a coating provides exceptional softness, overload resistance, thermal and mechanical stability and allows a significant increase in breakdown voltage to **> 7,5kV**. We offer this professional product in **20** most popular diameters from **Ø 0,15mm / SWG 38** to **Ø 2,00mm / SWG 14**

The wires are made of the highest quality copper of increased purity, insulated twice with a two-layer enamel based on polyesterimide with an outer polyamidoimide coat. The wires thus made are extremely durable and, by having a very low coefficient of friction of the wire surface, have excellent mechanical abrasion resistance, which allows high speed of winding on modern high-speed winders, have excellent resistance to vibration and oscillation, are resistant to all kinds of thermal overloads and are characterized by excellent resistance to aggressive chemical agents such as solvents, diluters, lyes, saturating agents, flood masses, transformer oil, cooling agents and freons. These wires are dedicated to all applications that place above-average strength and thermal requirements, for equipment operating in extremely variable conditions and temperatures, and in particular for all kinds of coils, filters, choke windings, motors, transformers, power tools, generators, chillers as well as for all service and hobby work.

Winding wires are available in packs containing **250 grams** of product. They are evenly and consistently wound on convenient to use and fully recyclable plastic spools, with outer diameter of **Ø = 50mm** with an internal guide hole **Ø = 20mm** and packed in a sealed cover made of transparent shrink film, which allows you to quickly find the wire you need to use on the shelf in the warehouse, protects against oxidation, dust or insulation getting dirty during storage and always guarantees the final Recipient the highest quality of the wires when removed from the package.

The wires have been made using **ISO 9001** and **ISO 14001** standards, are approved for use in **EU** markets and comply with the requirements of the environmental directives **RoHS-3** (2015/863/EU), **RoHS-2** (2011/65/EU), **RoHS** (2002/95/EU) and also comply with the requirements of **REACH** (Regulation 1907/2006) meeting regularly updated ECHA restrictions.

DN2E 200 winding wires supplied by **BQ** can be used both for professional windings exposed to very high overloads and work in extremely harsh conditions and for simple hobby work. They are an excellent choice for those who value quality, reliability and comfort.

BQ CABLE

