

432RS6B

Wall mounted socket

2CMA101026R1000



Surface socket outlets, 3P+N+E, IP44, 32 A, 200/346 ...
240/415 V

GENERAL

Product Name	Wall mounted socket
Product ID	2CMA101026R1000
Function	Outlet
EAN	739269269
Catalog Description	Surface socket outlets, 3P+N+E, 32 A, 200/346 ... 240/415 V
Country of Origin	Czech Republic (CZ)
E-Number Finland	2420321
E-Number Norway	1543470
E-Number Sweden	
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	85 millimetre
Product Net Height	121 millimetre
Product Net Length	164 millimetre
Product Net Depth	164 millimetre
Product Net Weight	0.35 kilogram

TECHNICAL

Product Main Type	ERS
Color	Red
Number of Poles	5
Clock Position	6Hour
Rated Current	32 ampere
Rated Voltage	200/346 ... 240/415 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	2.5...10 mm ²
Housing Material	Plastic (PA)
Plug Angle	
Product Group	Easy&Safe

PACKAGING

Package Width	175 millimetre
Package Height	188 millimetre
Package Gross Weight	3.5 kilogram
Package Length	428 millimetre
Package Units	box 10 piece