

216ERS4W

Wall mounted socket

2CMA101212R1000



Wall mounted outlet, 2P+E, 16A, 100 ... 130 V Clock Position
Of Grounding Contact 4 hour Color code Yellow

GENERAL

Product Name	Wall mounted socket
Product ID	2CMA101212R1000
Function	Wall mounted socket
EAN	73926912126
Catalog Description	Wall mounted outlets, 2P+E, 16A, 100 ... 130 V
Country of Origin	Czech Republic (CZ)
E-Number Finland	
E-Number Norway	
E-Number Sweden	
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	ERS
Color	Yellow
Number of Poles	3
Clock Position	4Hour
Rated Current	16 ampere
Rated Voltage	100 ... 130 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67
Cable Cross-Section	1...2.5 mm ²
Housing Material	Plastic (PA)
Plug Angle	
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	89 millimetre
Product Net Height	122 millimetre
Product Net Length	148 millimetre
Product Net Depth	148 millimetre
Product Net Weight	0.24 kilogram

PACKAGING

Package Width	134 millimetre
Package Height	467 millimetre
Package Gross Weight	1.2 kilogram
Package Length	177 millimetre
Package Units	box 5 piece