

332ERS9W

Wall mounted socket

2CMA101246R1000



Wall mounted outlet, 3P+E, 32A, 200 ... 250 V Clock Position
Of Grounding Contact 9 hour Color code Blue

GENERAL

Product Name	Wall mounted socket
Product ID	2CMA101246R1000
Function	Wall mounted socket
EAN	73926912461
Catalog Description	Wall mounted outlets, 3P+E, 32A, 200 ... 250 V
Country of Origin	Czech Republic (CZ)
E-Number Finland	
E-Number Norway	
E-Number Sweden	
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	89 millimetre
Product Net Height	117 millimetre
Product Net Length	163 millimetre
Product Net Depth	163 millimetre
Product Net Weight	0.32 kilogram

TECHNICAL

Product Main Type	ERS
Color	Blue
Number of Poles	4
Clock Position	9Hour
Rated Current	32 ampere
Rated Voltage	200 ... 250 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67
Cable Cross-Section	2.5...6 mm ²
Housing Material	Plastic (PA)
Plug Angle	
Product Group	Easy&Safe

PACKAGING

Package Width	134 millimetre
Package Height	467 millimetre
Package Gross Weight	1.6 kilogram
Package Length	177 millimetre
Package Units	box 5 piece