

416EP7W

Industrial Plug

2CMA101090R1000

Industrial Plugs, 3P+N+E, 16A, 277/480 ... 288/500 V Clock
Position Of Grounding Contact 7 hour Color code Black



GENERAL

Product Name	Industrial Plug
Product ID	2CMA101090R1000
Function	Plug
EAN	7392690
Catalog Description	Industrial Plugs, 3P+N+E, 16A, 277/480 ... 288/500 V
Country of Origin	Czech Republic (CZ)
E-Number Finland	2420105
E-Number Norway	
E-Number Sweden	
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	EP
Color	Black
Number of Poles	5
Clock Position	7Hour
Rated Current	16 ampere
Rated Voltage	480 ... 500 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67
Cable Cross-Section	1...2.5 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	87 millimetre
Product Net Height	87 millimetre
Product Net Length	160 millimetre
Product Net Depth	160 millimetre
Product Net Weight	0.21 kilogram

PACKAGING

Package Width	390 millimetre
Package Height	195 millimetre
Package Gross Weight	2.1 kilogram
Package Length	175 millimetre
Package Units	box 10 piece