

332EP9W

Industrial Plug

2CMA101105R1000

Industrial Plugs, 3P+E, 32A, 200 ... 250 V Clock Position Of
Grounding Contact 9 hour Color code Blue



GENERAL

Product Name	Industrial Plug
Product ID	2CMA101105R1000
Function	Plug
EAN	739269151
Catalog Description	Industrial Plugs, 3P+E, 32A, 200 ... 250 V
Country of Origin	Czech Republic (CZ)
E-Number Finland	
E-Number Norway	
E-Number Sweden	
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	EP
Color	Blue
Number of Poles	4
Clock Position	9Hour
Rated Current	32 ampere
Rated Voltage	200 ... 250 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67
Cable Cross-Section	2.5...6 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	91 millimetre
Product Net Height	91 millimetre
Product Net Length	183 millimetre
Product Net Depth	183 millimetre
Product Net Weight	0.25 kilogram

PACKAGING

Package Width	390 millimetre
Package Height	195 millimetre
Package Gross Weight	2.5 kilogram
Package Length	175 millimetre
Package Units	box 10 piece