

316EP11

Industrial Plug

2CMA101960R1000

Industrial Plugs, 3P+E, 16A, 440 ... 460 V Clock Position Of
Grounding Contact 11 hour Color code Red



GENERAL

Product Name	Industrial Plug
Product ID	2CMA101960R1000
Function	Plug
EAN	739269196
Catalog Description	Industrial Plugs, 3P+E, 16A, 440 ... 460 V
Country of Origin	Czech Republic (CZ)
E-Number Finland	
E-Number Norway	
E-Number Sweden	E2416168
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	EP
Color	Red
Number of Poles	4
Clock Position	11Hour
Rated Current	16 ampere
Rated Voltage	440 ... 460 volt
Frequency	60 hertz
Degree of Protection	IP44
Cable Cross-Section	1...2.5 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	69 millimetre
Product Net Height	75 millimetre
Product Net Length	144 millimetre
Product Net Depth	144 millimetre
Product Net Weight	0.16 kilogram

PACKAGING

Package Width	138 millimetre
Package Height	345 millimetre
Package Gross Weight	1.6 kilogram
Package Length	158 millimetre
Package Units	box 10 piece