

332EP7

# Industrial Plug

## 2CMA101985R1000

Industrial Plugs, 3P+E, 32A, 480 ... 500 V Clock Position Of  
Grounding Contact 7 hour Color code Black



## GENERAL

|                     |                                               |
|---------------------|-----------------------------------------------|
| Product Name        | Industrial Plug                               |
| Product ID          | 2CMA101985R1000                               |
| Function            | Plug                                          |
| EAN                 | 73926919859                                   |
| Catalog Description | Industrial Plugs, 3P+E,<br>32A, 480 ... 500 V |
| Country of Origin   | Czech Republic (CZ)                           |
| E-Number Finland    |                                               |
| E-Number Norway     |                                               |
| E-Number Sweden     | E2416175                                      |
| Standards           | IEC 60309-1, -2                               |
| RoHS Status         | Following EU Directive<br>2011/65/EU          |

## TECHNICAL

|                      |                         |
|----------------------|-------------------------|
| Product Main Type    | EP                      |
| Color                | Black                   |
| Number of Poles      | 4                       |
| Clock Position       | 7Hour                   |
| Rated Current        | 32 ampere               |
| Rated Voltage        | 480 ... 500 volt        |
| Frequency            | 50 hertz 60 hertz       |
| Degree of Protection | IP44                    |
| Cable Cross-Section  | 2.5...6 mm <sup>2</sup> |
| Housing Material     | Plastic (PA)            |
| Plug Angle           | Straight                |
| Product Group        | Easy&Safe               |

## DIMENSIONS

|                    |                |
|--------------------|----------------|
| Product Net Width  | 79 millimetre  |
| Product Net Height | 83 millimetre  |
| Product Net Length | 167 millimetre |
| Product Net Depth  | 167 millimetre |
| Product Net Weight | 0.23 kilogram  |

## PACKAGING

|                      |                |
|----------------------|----------------|
| Package Width        | 154 millimetre |
| Package Height       | 378 millimetre |
| Package Gross Weight | 2.3 kilogram   |
| Package Length       | 182 millimetre |
| Package Units        | box 10 piece   |