

232EC12W

Industrial Connector

2CMA101144R1000

Industrial Connectors, 2P+E, 32A, Isol. Transformer V Clock
Position Of Grounding Contact 12 hour Color code Grey



GENERAL

Product Name	Industrial Connector
Product ID	2CMA101144R1000
Function	Connector
EAN	739269114
Catalog Description	Industrial Connectors, 2P+E, 32A, Isol. Transformer V
Country of Origin	Czech Republic (CZ)
E-Number Finland	
E-Number Norway	
E-Number Sweden	
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	EC
Color	Grey
Number of Poles	3
Clock Position	12Hour
Rated Current	32 ampere
Rated Voltage	Isol. Transformer volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67
Cable Cross-Section	2.5...6 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	98 millimetre
Product Net Height	98 millimetre
Product Net Length	195 millimetre
Product Net Depth	195 millimetre
Product Net Weight	0.28 kilogram

PACKAGING

Package Width	390 millimetre
Package Height	195 millimetre
Package Gross Weight	2.8 kilogram
Package Length	175 millimetre
Package Units	box 10 piece