

332EC9W

Industrial Connector

2CMA101152R1000

Industrial Connectors, 3P+E, 32A, 200 ... 250 V Clock
Position Of Grounding Contact 9 hour Color code Blue



GENERAL

Product Name	Industrial Connector
Product ID	2CMA101152R1000
Function	Connector
EAN	73926911525
Catalog Description	Industrial Connectors, 3P+E, 32A, 200 ... 250 V
Country of Origin	Czech Republic (CZ)
E-Number Finland	
E-Number Norway	
E-Number Sweden	
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	98 millimetre
Product Net Height	98 millimetre
Product Net Length	195 millimetre
Product Net Depth	195 millimetre
Product Net Weight	0.30 kilogram

TECHNICAL

Product Main Type	EC
Color	Blue
Number of Poles	4
Clock Position	9Hour
Rated Current	32 ampere
Rated Voltage	200 ... 250 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67
Cable Cross-Section	2.5...6 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

PACKAGING

Package Width	390 millimetre
Package Height	195 millimetre
Package Gross Weight	3 kilogram
Package Length	175 millimetre
Package Units	box 10 piece