

416ERS7W

Wall mounted socket

2CMA101231R1000



Wall mounted outlet, 3P+N+E, 16A, 277/480 ... 288/500 V
Clock Position Of Grounding Contact 7 hour Color code Black

GENERAL

Product Name	Wall mounted socket
Product ID	2CMA101231R1000
Function	Wall mounted socket
EAN	73926912317
Catalog Description	Wall mounted outlets, 3P+N+E, 16A, 277/480 ... 288/500 V
Country of Origin	Czech Republic (CZ)
E-Number Finland	2420160
E-Number Norway	
E-Number Sweden	
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	ERS
Color	Black
Number of Poles	5
Clock Position	7Hour
Rated Current	16 ampere
Rated Voltage	480 ... 500 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67
Cable Cross-Section	1...2.5 mm ²
Housing Material	Plastic (PA)
Plug Angle	
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	89 millimetre
Product Net Height	119 millimetre
Product Net Length	151 millimetre
Product Net Depth	151 millimetre
Product Net Weight	0.30 kilogram

PACKAGING

Package Width	134 millimetre
Package Height	467 millimetre
Package Gross Weight	1.5 kilogram
Package Length	177 millimetre
Package Units	box 5 piece