

216C12W

Industrial Connector

2CMA166542R1000

Connector, earthing sleeve position 12h, rated current 16A, IP67 watertight, 2-poles+earth, frequency 50-60 Hz, color code Grey



GENERAL

Product Name	Industrial Connector
Product ID	2CMA166542R1000
Function	Connector
EAN	7392696665421
Catalog Description	Connector, 12h, 16A, IP67, 2P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2416363
E-Number Norway	2416363
E-Number Sweden	E2416363
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	TC
Color	Grey
Number of Poles	3
Clock Position	12Hour
Rated Current	16 ampere
Rated Voltage	Isol. Transformer volt
Frequency	50 hertz
Degree of Protection	IP67 IP69
Cable Cross-Section	1...2.5 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	Straight
Product Group	Tough&Safe

DIMENSIONS

Product Net Width	70 millimetre
Product Net Height	80 millimetre
Product Net Length	151 millimetre
Product Net Depth	151 millimetre
Product Net Weight	0.22 kilogram

PACKAGING

Package Width	95 millimetre
Package Height	175 millimetre
Package Gross Weight	0.22 kilogram
Package Length	95 millimetre
Package Units	box 1 piece