

332EBS9W

# Wall mounted inlet

## 2CMA101199R1000



Wall mounted inlet, 3P+E, 32A, 200 ... 250 V Clock Position  
Of Grounding Contact 9 hour Color code Blue

## GENERAL

|                     |                                                     |
|---------------------|-----------------------------------------------------|
| Product Name        | Wall mounted inlet                                  |
| Product ID          | 2CMA101199R1000                                     |
| Function            | Wall mounted inlet                                  |
| EAN                 | 739269119                                           |
| Catalog Description | Wall mounted inlets,<br>3P+E, 32A, 200 ... 250<br>V |
| Country of Origin   | Czech Republic (CZ)                                 |
| E-Number Finland    |                                                     |
| E-Number Norway     |                                                     |
| E-Number Sweden     |                                                     |
| Standards           | IEC 60309-1, -2                                     |
| RoHS Status         | Following EU Directive<br>2011/65/EU                |

## TECHNICAL

|                      |                         |
|----------------------|-------------------------|
| Product Main Type    | EBS                     |
| Color                | Blue                    |
| Number of Poles      | 4                       |
| Clock Position       | 9Hour                   |
| Rated Current        | 32 ampere               |
| Rated Voltage        | 200 ... 250 volt        |
| Frequency            | 50 hertz 60 hertz       |
| Degree of Protection | IP67                    |
| Cable Cross-Section  | 2.5...6 mm <sup>2</sup> |
| Housing Material     | Plastic (PA)            |
| Plug Angle           | Angled                  |
| Product Group        | Easy&Safe               |

## DIMENSIONS

|                    |                |
|--------------------|----------------|
| Product Net Width  | 89 millimetre  |
| Product Net Height | 105 millimetre |
| Product Net Length | 150 millimetre |
| Product Net Depth  | 150 millimetre |
| Product Net Weight | 0.27 kilogram  |

## PACKAGING

|                      |                |
|----------------------|----------------|
| Package Width        | 134 millimetre |
| Package Height       | 467 millimetre |
| Package Gross Weight | 1.35 kilogram  |
| Package Length       | 177 millimetre |
| Package Units        | box 5 piece    |