

216EBU6W

Panel mounted inlet

2CMA101259R1000



Panel mounted inlet, 2P+E, 16A, 200 ... 250 V Clock Position
Of Grounding Contact 6 hour Color code Blue

GENERAL

Product Name	Panel mounted inlet
Product ID	2CMA101259R1000
Function	Panel mounted inlet
EAN	73926912591
Catalog Description	Panel mounted inlets, 2P+E, 16A, 200 ... 250 V
Country of Origin	Czech Republic (CZ)
E-Number Finland	2420122
E-Number Norway	
E-Number Sweden	E2417654
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	85 millimetre
Product Net Height	94 millimetre
Product Net Length	65 millimetre
Product Net Depth	65 millimetre
Product Net Weight	0.11 kilogram

TECHNICAL

Product Main Type	EBU
Color	Blue
Number of Poles	3
Clock Position	6Hour
Rated Current	16 ampere
Rated Voltage	200 ... 250 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67
Cable Cross-Section	1...2.5 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

PACKAGING

Package Width	74 millimetre
Package Height	442 millimetre
Package Gross Weight	1.1 kilogram
Package Length	187 millimetre
Package Units	box 10 piece