

332EC3

Industrial Connector

2CMA102037R1000

Industrial Connectors, 3P+E, 32A, 380/440 V Clock Position
Of Grounding Contact 3 hour Color code Red



GENERAL

Product Name	Industrial Connector
Product ID	2CMA102037R1000
Function	Connector
EAN	739269374
Catalog Description	Industrial Connectors, 3P+E, 32A, 380/440 V
Country of Origin	Czech Republic (CZ)
E-Number Finland	
E-Number Norway	
E-Number Sweden	E2416062
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	EC
Color	Red
Number of Poles	4
Clock Position	3Hour
Rated Current	32 ampere
Rated Voltage	380/440 volt
Frequency	50/60 hertz
Degree of Protection	IP44
Cable Cross-Section	2.5...6 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	79 millimetre
Product Net Height	93 millimetre
Product Net Length	182 millimetre
Product Net Depth	182 millimetre
Product Net Weight	0.28 kilogram

PACKAGING

Package Width	154 millimetre
Package Height	378 millimetre
Package Gross Weight	2.8 kilogram
Package Length	182 millimetre
Package Units	box 10 piece