

432EC11

Industrial Connector

2CMA102054R1000



Industrial Connectors, 3P+N+E, 32A, 250/440 ... 265/460 V
Clock Position Of Grounding Contact 11 hour Color code Red

GENERAL

Product Name	Industrial Connector
Product ID	2CMA102054R1000
Function	Connector
EAN	739269541
Catalog Description	Industrial Connectors, 3P+N+E, 32A, 250/440 ... 265/460 V
Country of Origin	Czech Republic (CZ)
E-Number Finland	
E-Number Norway	
E-Number Sweden	
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	EC
Color	Red
Number of Poles	5
Clock Position	11Hour
Rated Current	32 ampere
Rated Voltage	250/440 ... 265/460 volt
Frequency	60 hertz
Degree of Protection	IP44
Cable Cross-Section	2.5...6 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	79 millimetre
Product Net Height	99 millimetre
Product Net Length	183 millimetre
Product Net Depth	183 millimetre
Product Net Weight	0.3 kilogram

PACKAGING

Package Width	154 millimetre
Package Height	378 millimetre
Package Gross Weight	3 kilogram
Package Length	182 millimetre
Package Units	box 10 piece