

332C7W

Industrial Connector

2CMA166606R1000

Connector, earthing sleeve position 7h, rated current 32A, IP67 watertight, 3-poles+earth, frequency 50-60 Hz, color code Black



GENERAL

Product Name	Industrial Connector
Product ID	2CMA166606R1000
Function	Connector
EAN	739269666
Catalog Description	Connector, 7h, 32A, IP67, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421714
E-Number Norway	2416393
E-Number Sweden	E2416393
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	TC
Color	Black
Number of Poles	4
Clock Position	7Hour
Rated Current	32 ampere
Rated Voltage	480 ... 500 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67 IP69
Cable Cross-Section	2.5...6 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	Straight
Product Group	Tough&Safe

DIMENSIONS

Product Net Width	91 millimetre
Product Net Height	102 millimetre
Product Net Length	184 millimetre
Product Net Depth	184 millimetre
Product Net Weight	0.408 kilogram

PACKAGING

Package Width	135 millimetre
Package Height	200 millimetre
Package Gross Weight	0.474 kilogram
Package Length	140 millimetre
Package Units	box 1 piece