

332P5W

Industrial Plug

2CMA166736R1000

Plug, earthing sleeve position 5h, rated current 32A, IP67 watertight, 3-poles+earth, frequency 50-60 Hz, color code Black



GENERAL

Product Name	Industrial Plug
Product ID	2CMA166736R1000
Function	Plug
EAN	7392696667364
Catalog Description	Plug, 5h, 32A, IP67, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421643
E-Number Norway	2416267
E-Number Sweden	E2416267
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	TP
Color	Black
Number of Poles	4
Clock Position	5Hour
Rated Current	32 ampere
Rated Voltage	600 ... 690 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67 IP69
Cable Cross-Section	2.5...6 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	Straight
Product Group	Tough&Safe

DIMENSIONS

Product Net Width	94 millimetre
Product Net Height	94 millimetre
Product Net Length	147 millimetre
Product Net Depth	147 millimetre
Product Net Weight	0.3 kilogram

PACKAGING

Package Width	95 millimetre
Package Height	175 millimetre
Package Gross Weight	0.4 kilogram
Package Length	95 millimetre
Package Units	box 1 piece