

432EP6B

Industrial Plug

2CMA103593R1000

Industrial Plug, 432EP6B, 32 A, 3P+N+E, 6 hour, Industrial plugs, 3P+N+E, 32 A, 200/346 ... 240/415V,



GENERAL

Product Name	Industrial Plug
Product ID	2CMA103593R1000
Function	Plug
EAN	73926935934
Catalog Description	Industrial plugs, 3P+N+E, 32 A, 200/346 ... 240/415V
Country of Origin	Czech Republic (CZ)
E-Number Finland	2420243
E-Number Norway	1540765
E-Number Sweden	E2417575
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	EP
Color	Red
Number of Poles	5
Clock Position	6Hour
Rated Current	32 ampere
Rated Voltage	200/346 ... 240/415 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	2.5...6 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	79 millimetre
Product Net Height	88 millimetre
Product Net Length	167 millimetre
Product Net Depth	167 millimetre
Product Net Weight	0.24 kilogram

PACKAGING

Package Width	154 millimetre
Package Height	378 millimetre
Package Gross Weight	2.4 kilogram
Package Length	182 millimetre
Package Units	box 10 piece