

316P7W

Industrial Plug

2CMA166478R1000

Plug, earthing sleeve position 7h, rated current 16A, IP67 watertight, 3-poles+earth, frequency 50-60 Hz, color code Black



GENERAL

Product Name	Industrial Plug
Product ID	2CMA166478R1000
Function	Plug
EAN	7392696664783
Catalog Description	Plug, 7h, 16A, IP67, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421635
E-Number Norway	2416246
E-Number Sweden	E2416246
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	TP
Color	Black
Number of Poles	4
Clock Position	7Hour
Rated Current	16 ampere
Rated Voltage	480 ... 500 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67 IP69
Cable Cross-Section	1...2.5 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	Straight
Product Group	Tough&Safe

DIMENSIONS

Product Net Width	79 millimetre
Product Net Height	79 millimetre
Product Net Length	144 millimetre
Product Net Depth	144 millimetre
Product Net Weight	0.24 kilogram

PACKAGING

Package Width	95 millimetre
Package Height	175 millimetre
Package Gross Weight	0.24 kilogram
Package Length	95 millimetre
Package Units	box 1 piece