

416EP6B

Industrial Plug

2CMA103591R1000

Industrial Plug, 416EP6B, 16 A, 3P+N+E, 6 hour, Industrial
plugs, 3P+N+E, 16 A, 200/346 ... 240/415V,



GENERAL

Product Name	Industrial Plug
Product ID	2CMA103591R1000
Function	Plug
EAN	739269359
Catalog Description	Industrial plugs, 3P+N+E, 16 A, 200/346 ... 240/415V
Country of Origin	Czech Republic (CZ)
E-Number Finland	2420235
E-Number Norway	1540761
E-Number Sweden	E2417572
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	EP
Color	Red
Number of Poles	5
Clock Position	6Hour
Rated Current	16 ampere
Rated Voltage	200/346 ... 240/415 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	1...2.5 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	69 millimetre
Product Net Height	78 millimetre
Product Net Length	144 millimetre
Product Net Depth	144 millimetre
Product Net Weight	0.18 kilogram

PACKAGING

Package Width	154 millimetre
Package Height	378 millimetre
Package Gross Weight	1.8 kilogram
Package Length	182 millimetre
Package Units	box 10 piece