

432EC6B

Industrial Connector

2CMA103592R1000

Industrial connectors, 3P+N+E, IP44, 32 A, V



GENERAL

Product Name	Industrial Connector
Product ID	2CMA103592R1000
Function	Connector
EAN	73926935927
Catalog Description	Industrial connectors, 3P+N+E, 32 A, 200/346 ... 240/415V
Country of Origin	Czech Republic (CZ)
E-Number Finland	2420314
E-Number Norway	1540773
E-Number Sweden	E2417581
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	79 millimetre
Product Net Height	99 millimetre
Product Net Length	183 millimetre
Product Net Depth	183 millimetre
Product Net Weight	0.3 kilogram

TECHNICAL

Product Main Type	EC
Color	Red
Number of Poles	5
Clock Position	6Hour
Rated Current	32 ampere
Rated Voltage	200/346 ... 240/415 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	2.5...6 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

PACKAGING

Package Width	154 millimetre
Package Height	378 millimetre
Package Gross Weight	3 kilogram
Package Length	182 millimetre
Package Units	box 10 piece