

363P11

Industrial Plug

2CMA166758R1000

Plug, earthing sleeve position 11h, rated current 63A, IP44 splashproof, 3-poles+earth, frequency 60 Hz, color code Red



GENERAL

Product Name	Industrial Plug
Product ID	2CMA166758R1000
Function	Plug
EAN	7392696667586
Catalog Description	Plug, 11h, 63A, IP44, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2416229
E-Number Norway	2416229
E-Number Sweden	E2416229
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	TP
Color	Red
Number of Poles	4
Clock Position	11Hour
Rated Current	63 ampere
Rated Voltage	440 ... 460 volt
Frequency	60 hertz
Degree of Protection	IP44
Cable Cross-Section	4...16 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	Straight
Product Group	Tough&Safe

DIMENSIONS

Product Net Width	103 millimetre
Product Net Height	103 millimetre
Product Net Length	215 millimetre
Product Net Depth	215 millimetre
Product Net Weight	0.64 kilogram

PACKAGING

Package Width	114 millimetre
Package Height	230 millimetre
Package Gross Weight	0.72 kilogram
Package Length	114 millimetre
Package Units	box 1 piece