

363P7W

Industrial Plug

2CMA166788R1000

Plug, earthing sleeve position 7h, rated current 63A, IP67 watertight, 3-poles+earth, frequency 50-60 Hz, color code Black



GENERAL

Product Name	Industrial Plug
Product ID	2CMA166788R1000
Function	Plug
EAN	7392696667883
Catalog Description	Plug, 7h, 63A, IP67, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421640
E-Number Norway	1563675
E-Number Sweden	E2416289
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	TP
Color	Black
Number of Poles	4
Clock Position	7Hour
Rated Current	63 ampere
Rated Voltage	480 ... 500 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67 IP69
Cable Cross-Section	4...16 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	Straight
Product Group	Tough&Safe

DIMENSIONS

Product Net Width	114 millimetre
Product Net Height	114 millimetre
Product Net Length	275 millimetre
Product Net Depth	275 millimetre
Product Net Weight	1.05 kilogram

PACKAGING

Package Width	120 millimetre
Package Height	285 millimetre
Package Gross Weight	1.14 kilogram
Package Length	138 millimetre
Package Units	box 1 piece