

263C6

Industrial Connector

2CMA166840R1000



Connector, earthing sleeve position 6h, rated current 63A, IP44 splashproof, 2-poles+earth, frequency 50-60 Hz, color code Blue

GENERAL

Product Name	Industrial Connector
Product ID	2CMA166840R1000
Function	Connector
EAN	73926966688
Catalog Description	Connector, 6h, 63A, IP44, 2P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421705
E-Number Norway	1565360
E-Number Sweden	E2416345
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	TC
Color	Blue
Number of Poles	3
Clock Position	6Hour
Rated Current	63 ampere
Rated Voltage	200 ... 250 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	4...16 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	Straight
Product Group	Tough&Safe

DIMENSIONS

Product Net Width	98 millimetre
Product Net Height	112 millimetre
Product Net Length	224 millimetre
Product Net Depth	224 millimetre
Product Net Weight	0.8 kilogram

PACKAGING

Package Width	114 millimetre
Package Height	230 millimetre
Package Gross Weight	0.88 kilogram
Package Length	114 millimetre
Package Units	box 1 piece